

## TEST 134 serial number: 07

### cotton dyed with Direct orange 39

#### generally:

according:	Swissatest colour transfer monitors		
suitable:	For assessing colour transfer within a washing process.		
date of production:	June 2018		
durability:	unlimited		
storing conditions:	must be well packed and kept in the dark		

## specification of base material:

article 211	cotton fabric, percale, bleached, without optical brightener			
thread count in cm	warp: 46			
	weft: 46			
yarn count in Tex	warp: 100			
	weft: 100			
weight in g/m <sup>2</sup>	90.0			
width in cm	152.0			
Y-value	90.2			
Rem <sub>460nm</sub>	87.8			

## specification of soiled fabric:

soiling	dyed with Direct orange 39 with a textile deveing process dyestuff, substantive dyestuf		
weight in g/m <sup>2</sup>	92.0		
width in cm	152.0		
Y-value	26.3		
Rem <sub>460nm</sub>	4.1		

measuring conditions:

instrument

DC800V (spectrophotometer)

illuminant / observer

D65 / 10°

measuring geometry

d/8°

wavelength range

420 to 750nm

filter

UV barrier at 420nm

measuring diameter

26 mm

gloss

excluded





# Data sheet for article 134 Direct Orange 39 on cotton

Serial: 7

washing colour fastness	A1S	A2S	C1S	C2S
Changing	3.5	4	3	3.5
staining on:				
Triacetate filament	5	5	5	5
Bleached cotton	1.5	1.5	1	1
Polyamide 6.6 spun	4.5	4.5	3.5	3
Polyester, type 54 spun	5	5	4.5	4.5
Polyacrylnitrile, type 75 spun	5	5	4.5	5
Viscose spun type	2	2	1	1

#### Dry and wet rub fastness:

dry: 4.8 wet: 2.5

#### Description of the washing colour fastness:

Norm: ISO / EN 105-C06

A1S: 40°C, 30 min. 4 g/l ECE detergent A2S: 40°C, 30 min. 4 g/l ECE detergent

1 g/l perborate

A2S: 60°C, 30 min. 4 g/l ECE detergent

pH 10.5 with soda

A2S: 60°C, 30 min. 4 g/l ECE detergent

1 g/l perborate pH 10.5 with soda

Measuring conditions:

Instrument: DC 800V (Spectrophotometer)

Illuminant / observer: D65 / 10°
Measuring geometry: d/8°
Wavelength range: 420 to 750nm

UV filter: UV barrier at 420nm

Measuring diameter: 9 mm
Gloss: excluded

Measuring program: Sedo Treepoint, QTex 2.8.2.0